

Cross-sec. mm ²	Outer Ø min. - max. mm	Cop. weight kg / km	RD/WH	BU/WH	BN/WH	D-BU/WH
----------------------------	------------------------	---------------------	-------	-------	-------	---------



Packing

Coil in cardboard (100m)

H05V-K coil						
Part no. 0,5	2,1 - 2,5	4,8	29370	29375	29380	29394
Part no. 0,75	2,2 - 2,7	7,2	29371	29376	29381	29395
Part no. 1	2,4 - 2,8	9,6	29372	29377	29382	29396

Packing

Coil in cardboard (100m)

(H)07V-K coil						
Part no. 1,5	2,8 - 3,4	14,4	29373	29378	29383	29397
Part no. 2,5	3,4 - 4,1	24,0	29374	29379	29384	29398
Part no. 4	3,9 - 4,8	38,0	29385	29386	29387	29399
Part no. 6	4,4 - 5,3	58,0	29388	29389	29390	29527
Part no. 10	5,7 - 6,8	96,0	29391	29392	29393	29528



Packing

Spool (with various capacity)

H05V-K spool						
Part no. 0,5	2,1 - 2,5	4,8	29745	29746	29747	29748
Part no. 0,75	2,2 - 2,7	7,2	29749	29750	29751	29752
Part no. 1	2,4 - 2,8	9,6	29753	29754	29755	29756

Packing

Spool (with various capacity)

(H)07V-K spool						
Part no. 1,5	2,8 - 3,4	14,4	29757	29758	29759	29760
Part no. 2,5	3,4 - 4,1	24,0	29761	29762	29763	29764
Part no. 4	3,9 - 4,8	38,0	29765	29766	29767	29768
Part no. 6	4,4 - 5,3	58,0	29769	29770	29771	29772
Part no. 10	5,7 - 6,8	96,0	29773	29774	29775	29776



Packing

Barrel (with various capacity)

H05V-K barrel						
Part no. 0,5	2,1 - 2,5	4,8	28948	28949	28950	28951
Part no. 0,75	2,2 - 2,7	7,2	28952	28953	28954	28955
Part no. 1	2,4 - 2,8	9,6	28956	28957	28958	28959

Packing

Barrel (with various capacity)

(H)07V-K barrel						
Part no. 1,5	2,8 - 3,4	14,4	28960	28961	28962	28963
Part no. 2,5	3,4 - 4,1	24,0	28964	28965	28966	28967
Part no. 4	3,9 - 4,8	38,0	28968	28969	28970	28971
Part no. 6	4,4 - 5,3	58,0	28972	28973	28974	28975
Part no. 10	5,7 - 6,8	96,0	28976	28977	28978	28979

Dimensions and specifications may be changed without prior notice.