



Cat.6A S/FTP Patch Cable, GHMT Certified

Technical Features

Cat.6A Class EA 500MHz

Gold Contact

Shielding: 0.12mm*80 alu-mg wire braiding

26/7AWG copper wire, pairs in metal foil (PIMF)

Low smoke zero halogen jacket, Ø6mm

Certified by GHMT

Length	Grey	EAN Code
0.50 m	CQ5022S	4052792037500
1.00 m	CQ5032S	4052792037517
1.50 m	CQ5042S	4052792037524
2.00 m	CQ5052S	4052792037531
3.00 m	CQ5062S	4052792037548
5.00 m	CQ5072S	4052792037555
7.50 m	CQ5082S	4052792037562
10.00 m	CQ5092S	4052792037579
15.00 m	CQ5102S	4052792037586
20.00 m	CQ5112S	4052792037593



www.logilink.de



RoHS
compliant



Made in China

* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered namework of their respective owners.

Length	Red	EAN Code	Green	EAN Code
0.50 m	CQ5024S	4052792037616	CQ5025S	4052792037722
1.00 m	CQ5034S	4052792037623	CQ5035S	4052792037739
1.50 m	CQ5044S	4052792037630	CQ5045S	4052792037746
2.00 m	CQ5054S	4052792037647	CQ5055S	4052792037753
3.00 m	CQ5064S	4052792037654	CQ5065S	4052792037760
5.00 m	CQ5074S	4052792037661	CQ5075S	4052792037777
7.50 m	CQ5084S	4052792037678	CQ5085S	4052792037784
10.00 m	CQ5094S	4052792037685	CQ5095S	4052792037791
15.00 m	CQ5104S	4052792037692	CQ5105S	4052792037807
20.00 m	CQ5114S	4052792037708	CQ5115S	4052792037814

Length	Blue	EAN Code
0.50 m	CQ5026S	4052792037838
1.00 m	CQ5036S	4052792037845
1.50 m	CQ5046S	4052792037852
2.00 m	CQ5056S	4052792037869
3.00 m	CQ5066S	4052792037876
5.00 m	CQ5076S	4052792037883
7.50 m	CQ5086S	4052792037890
10.00 m	CQ5096S	4052792037906
15.00 m	CQ5106S	4052792037913
20.00 m	CQ5116S	4052792037920



Length	Yellow	EAN Code
0.50 m	CQ5027S	4052792037944
1.00 m	CQ5037S	4052792037951
1.50 m	CQ5047S	4052792037968
2.00 m	CQ5057S	4052792037975
3.00 m	CQ5067S	4052792037982
5.00 m	CQ5077S	4052792037999
7.50 m	CQ5087S	4052792038002
10.00 m	CQ5097S	4052792038019
15.00 m	CQ5107S	4052792038026
20.00 m	CQ5117S	4052792038033



Package Contents

CAT6A S/FTP Patch Cable, GHMT Certified x 1

Packaging Informations

Packing Dimension	150 x 130 x 50mm (0.5m)/160 x 140 x 50mm (1-2m)/180 x 160 x 50mm (3-5m)/200 x 200 x 50mm (7.5-10m)/200 x 200 x 100mm (15m)/240 x 200 x 100mm (20m)
Packing Weight	0.03kg (0.5m)/0.04kg (1m)/0.06kg (1.5m)/0.07kg (2m)/0.11kg (3m)/0.19kg (5m)/0.26kg (7.5m)/0.34kg (10m)/0.51kg (15m)/0.66kg (20m)
Carton Dimension	400 x 300 x 300mm
Carton Q'ty	160pcs (0.5m)/120pcs (1m)/100pcs (1.5m)/80pcs (2m)/60pcs (3m)/50pcs (5m)/30pcs (7.5m)/25pcs (10m)/20pcs (15m)/15pcs (20m)
Carton Weight	7.54kg (0.5m)/8.2kg (1m)/8.7kg (1.5m)/8.72kg (2m)/8.44kg (3m)/10.62kg (5m)/9.25kg (7.5m)/9.5kg (10m)/10.9kg (15m)/11kg (20m)

www.logilink.de



RoHS
compliant



Made in China

* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered trademark of their respective owners.