


# PAO TYPE



ITEM NO.	A	B	C
PA0-07	6.0±0.25	9.8±0.35	2.6±0.3
PA0-10	9.0±0.25	13.0±0.35	2.2±0.3
PA0-12	11.4±0.35	15.5±0.35	2.3±0.3
PA0-17	16.3±0.35	21.6±0.45	2.6±0.3
PA0-23	22.4±0.45	28.2±0.45	2.4±0.3
PA0-29	27.9±0.45	34.0±0.45	2.7±0.3
PA0-36	35.8±0.45	42.4±0.6	2.3±0.3
PA0-48	47.5±0.6	54.5±0.6	2.3±0.3

承認

審查

製圖

設計

中文名 尼龍浪管(剖開型)		MATERIAL NYLON6	ITEM NO. PAO TYPE
SCALE	FINISH	NAME NYLON FLEXIBLE CONDUIT(SPLIT DESIGN)	

△ ( )	TOLERANCE AS FIGURE	△ ( ) 08-26-2015 DATE	REVISIONS K001	R.NO.
-------	------------------------	-----------------------------	-------------------	-------

使用機種

