



## **In-wall CL3 High Speed HDMI Cable with Ethernet**

HEC, ARC, 3D, 4K, in-wall rated HDMI Male to Male, Shielded, Black, 10 m (33 ft.)

Part No.: **353977**

---

High Speed Cables deliver high-definition performance with in-wall rated safety measures.

HDMI has become the standard digital connection, delivering the highest-quality audio and video signal over a single cable. Manhattan CL3 High Speed HDMI Cables are rated for in-wall installation and feature an abrasion-resistant design, a sturdy yet flexible PVC jacket and gold-plated contacts. Created to meet the evolving needs of the high-definition marketplace and fire protection standards, this cable provides the highest resolution possible at 4K x 2K, an audio return channel and a bandwidth of 18 Gbps at 600 MHz. These high-quality cables deliver high-definition video and multichannel, digital audio with increased performance characteristics and greater accuracy. With its fully tested high specifications and in-wall fire rating, the Manhattan CL3 High Speed HDMI Cable will future-proof your Audio/Video project for years to come.

### **Features:**

- Supports HDMI Ethernet Channel, Audio Return Channel, 3D Video, 4K@60Hz Display and Deep Color
- CL3 rating for in-wall HDMI installations safeguards against potential fire risks
- 4K, UHD resolution supports video resolution 4 times 1080p; up to 1080p resolution in 3D and Deep Color
- ARC-allows TV's audio to transmit through your audio system; no need for additional audio cable
- High-speed Ethernet, bi-directional networking at up to 100 Mbps
- Up to 18 Gbps at 600 MHz bandwidth
- State-of-the-art cables future-proof in-home or office HDMI projects
- Compliant with High Speed HDMI with Ethernet specifications
- Double shielded to reduce EMI and other interference sources
- Compatible with any HDMI device, such as Blu-ray, game consoles, stereos, PCs and more
- Lifetime Warranty

### **Specifications:**

For more information on Manhattan products, consult your local dealer or visit [www.manhattan-products.com](http://www.manhattan-products.com). All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

Standards and Certifications:

- CL3
- CM
- UL 20276
- ISO 9002

General:

- Bandwidth: 18 Gbps at 600 MHz
- HEC support
- Meets or exceeds existing HDMI standards
- Length: 10 m (33 ft.)

Connectors:

- (2) HDMI 19-pin male
- Gold-plated contacts
- Molded PVC boot
- Built-in strain relief

Cable:

- 24 AWG cable
- Double shielded
- Current rating: 0.5 A DC
- Withstanding voltage: 300 V DC
- Insulation resistance: 10 MOhms
- Conductive resistance: 5 Ohms
- Thermal plastic casing

Package Contents:

- In-wall CL3 High Speed HDMI Cable with Ethernet Channel



