



In-wall CL3 High Speed HDMI Cable with Ethernet

HEC, ARC, 3D, 4K, in-wall rated HDMI Male to Male, Shielded, Black, 2 m (6 ft.)

Part No.: **353939**

High Speed Cables deliver high-definition performance with in-wall rated safety measures.

HDMI has become the standard digital connection, delivering the highest-quality audio and video signal over a single cable. Manhattan CL3 High Speed HDMI Cables are rated for in-wall installation and feature an abrasion-resistant design, a sturdy yet flexible PVC jacket and gold-plated contacts. Created to meet the evolving needs of the high-definition marketplace and fire protection standards, this cable provides the highest resolution possible at 4K x 2K, an audio return channel and a bandwidth of 18 Gbps at 600 MHz. These high-quality cables deliver high-definition video and multichannel, digital audio with increased performance characteristics and greater accuracy. With its fully tested high specifications and in-wall fire rating, the Manhattan CL3 High Speed HDMI Cable will future-proof your Audio/Video project for years to come.

Features:

- Supports HDMI Ethernet Channel, Audio Return Channel, 3D Video, 4K@60Hz Display and Deep Color
- CL3 rating for in-wall HDMI installations safeguards against potential fire risks
- 4K, UHD resolution supports video resolution 4 times 1080p; up to 1080p resolution in 3D and Deep Color
- ARC-allows TV's audio to transmit through your audio system; no need for additional audio cable
- High-speed Ethernet, bi-directional networking at up to 100 Mbps
- Up to 18 Gbps at 600 MHz bandwidth
- State-of-the-art cables future-proof in-home or office HDMI projects
- Compliant with High Speed HDMI with Ethernet specifications
- Double shielded to reduce EMI and other interference sources
- Compatible with any HDMI device, such as Blu-ray, game consoles, stereos, PCs and more
- Lifetime Warranty

Specifications:

Standards and Certifications:

- CL3
- CM
- UL 20276
- ISO 9002

General:

- Bandwidth: 18 Gbps at 600 MHz
- HEC support
- Meets or exceeds existing HDMI standards
- Length: 2 m (6 ft.)

Connectors:

- (2) HDMI 19-pin male
- Gold-plated contacts
- Molded PVC boot
- Built-in strain relief

Cable:

- 30 AWG cable
- Double shielded
- Current rating: 0.5 A DC
- Withstanding voltage: 300 V DC
- Insulation resistance: 10 MOhms
- Conductive resistance: 5 Ohms
- Thermal plastic casing

Package Contents:

- In-wall CL3 High Speed HDMI Cable with Ethernet Channel



