



NEW DMX COB RGB

EUROLITE LED PML-80 COB RGB 80W Spot/Wash
Color changer for continuous operation with 80 W COB LED

- Different radiation angles (from approx. 16° to approx. 36°) possible via additional lens (included with delivery)
- Flicker-free projection
- Dimmer speed (step response) adjustable
- Convection cooling entirely via cooling ribs, no fans, particularly quiet during operation

No. 41602595

Technical specifications:

Power supply:	100-240 V AC, 50/60 Hz ~
Power consumption:	65 W
DMX control channels:	3/5/6/7/8
DMX512 connection:	3-pin XLR
Sound-control:	via built-in microphone
Number of LEDs:	1
LED type:	80 W COB, RGB
Beam angle:	16°/36°
Dimensions (LxWxH):	175 x 169 x 257 mm
Weight:	2 kg



NEW DMX WW RDM

EUROLITE LED THA-40PC Theater Spot
Small and robust LED theatre spot

- Equipped with one 40 W WW LED
- CRI of >90
- Color temperature: 3000K
- With a plano-convex lens
- Supports RDM (Remote Device Management)
- Flicker-free projection
- Manual, stepless zoom

No. 41602080

Technical specifications:

Power supply:	100-240 V AC, 50/60 Hz ~
Power consumption:	40 W
DMX control channels:	1/2
DMX512 connection:	3-pin XLR
Type of LEDs:	40 W, warm white
Number of LEDs:	1
Color temperature:	3000 K
Beam angle:	11-37°
Dimensions (LxWxH):	334 x 195.3 x 172.7 mm
Weight:	3.6 kg



NEW DMX RGBW COB RDM

EUROLITE LED THA-60PC Theater Spot
LED theatre spot with barn doors and color filter frame

- Equipped with one 60 W COB LED in the colors red, green, blue and white
- With plano-convex lens
- Supports RDM (Remote Device Management)
- Flicker-free projection
- 5, 6 or 7 DMX channels selectable
- Manual, stepless zoom
- Rotatable barn doors and color filter frame included in the delivery

No. 41602110

Technical specifications:

Power supply:	100-240 V AC, 50/60 Hz ~
Power consumption:	60 W
DMX control channels:	5/6/7
DMX512 connection:	3-pin XLR
Type of LEDs:	60 W COB LED
Number of LEDs:	1
Beam angle:	7-39°
Dimensions (LxWxH):	334 x 195.3 x 172.7 mm
Weight:	3.6 kg

