



Type:	57966	Systems to charge:	Li-ion
Designation:	12000mAh slim power bank	Cell sizes:	Li-polymer
		Cell Configurations:	6000mAh, 2pc
Dimensions:	Charger:		
Length:	153 mm		
Width:	115 mm		
Height:	13 mm		
Weight:	390 g		
Charging methods:	Plug in Micro USB port :		
Input:	Current: 2000mA		
Discharging methods:	USB and type C port for charging other devices:		
Output1: USB	5.0V 3000mA		
Output2: type C	5.0V 3000mA		
Housing:		Indications: LED display	
Housing Material:	Aluminium	User Display-Status: Charging	Capacity0-25% LED1 flashing Capacity25-50% LED1 on LED2 flashing Capacity50-75% LED1-2 on LED3 flashing Capacity75-99% LED1-3 on LED4 flashing Capacity100% LED1-4 solid on
Casing colour:	Depending on PO	User Display-Status: Discharging	4 Blue LED = 100-76% Remaining 3 Blue LED = 51-75% Remaining 2 Blue LED = 26-50% Remaining 1 Blue LED = 3-25% Remaining 1 Flashing Blue LED = < 3% Remaining
Cover colour:	Depending on PO		
Power In:		Power Out:	
Primary:	5V DC 2000mA	Primary:	3.7V DC
Secondary:	3.7 V DC	Secondary:	5V DC 3000mA
Cut off criteria:			
Li-ion cells:	Stop discharging when Li-ion voltage lower than 2.8V		
	Short circuit protection		
	Overload protection		

No publication or circulation of data to third parties without consent of Spectrum Brands.