

IRIScan™ Book 5

The flatbed scanner killer is born!

IRIScan™ Book 5 is a light, autonomous, standalone, high resolution and lithium battery powered portable color scanner that allows you to scan magazines pages, books pages or letter & A4 documents such as invoices, contracts or even your favorite recipes. All this without having to rip pages off and damaging original support of document. It's the world's fastest portable autonomous scanner with down to 1 sec. scan per document. Simply roll your way across the document and your scan will be saved automatically into the provided MicroSD™ card, ready to be transferred onto your PC or Mac. Once back at home, hotel or in the office, the scanned documents are automatically turned into editable documents by the worldwide used IRIS' flagship OCR software Readiris™

In other words, it offers exactly what a regular flatbed scanner may offer but scans faster, anywhere, on any kind of document support without damaging it, and without warming up time needed, it gets the same image resolution level and all this on the go, without the need of a computer! A new era of scanning just begun, let's then enjoy this powerful liberty of document capture solution on the go with IRIScan Book!

Key features

Mobile scanner

- Specially convenient for Sales Rep & Product Marketers (Press article, flyers, ads, product competitor specs, ...); Logistic sector (warehouse clerk, packing slip, invoice, Air Way Bill, CMR,...); Legal & Insurance sector (complaints' documents, disaster documents, ...); Health sector (Doctor's prescription, health insurances' document refund, Pharmacy, ...); Education sector (student's lessons, courses documentation, training ...)
- Cordless, fully portable & autonomous. Carry it anywhere!
- Ideal to scan books, magazines & newspapers without tearing off pages.
- 300/600/1200 dpi scanning resolutions for perfect images results.
- Scanning speed: 1 sec. for a B&W document/ 2 sec. for a color document.
- Directly scan to PDF and JPEG. Create multi-page PDF files.
- Save scans onto the provided MicroSD™ card.
- 1.5" Color screen (be safe you scan correctly).
- Scan up to a 100 documents daily
- Powered by a lithium-ion USB rechargeable battery
- InstantResult function: real time appearing of your scans on your PC screen.

Quick reference guide

Product name	IRIScan™ Book 5 White/Red/Turquoise
SKU	458743 (White) / 458744 (Red) / 458745 (Turquoise)
UPC code	765010738915 (White) 765010738922 (Red) 765010738939 (Turquoise)
Custom code	847190
Box size (H x L x D)	13,8 x 31,2 x 4,8 cm (5.43 x 12.28 x 1.88 in)
Box weight	550 gr (19.4 oz)
Scanner size (H x L x D)	2,2 x 25,9 x 3,8 cm (0.87 x 10.19 x 1.49 in)
Scanner weight	153gr (5.4 oz)
Box languages	Arabic, Simplified Chinese, English, French, German, Italian, Portuguese, Russian, Spanish
Box content	IRIScan™ Book 5 scanner - Readiris Pro & IRISCompressor Pro software for PC & Mac available via download at www.irislink.com/start - One SD card - USB cable - Transport pouch.

Specifications	
Image sensor	Image sensor A4 color contact image sensor (CIS)
Resolution	300/600/1200 dpi
Scanning speed for A4 page	Color high resolution : 4 seconds Black & white high resolution : 3 seconds Color low resolution : 2 seconds Black & white low resolution : 1 second
Capacity (A4 documents, based on 4 GB MicroSD™ card. Depends on the content complexity)	1200 dpi color : 500 JPEG images
	600 dpi color : 1000 JPEG images
	300 dpi color : 2000 JPEG images
File format	JPEG, PDF or Multi-page PDF
LCD	1.5" Color with scanning status display/preview
USB port	Micro USB
External memory capacity	MicroSD™ card / MicroSDHC™ card up to 32 GB
Battery type	Built-in rechargeable Lithium battery/ 3.7 V
Battery life (scanning to MicroSD™ Card)	100 pages daily after recharging (A4, 300 dpi, color)

Official certificates of compliance are available at: www.irislink.com/certificates

Minimum requirements

For Computer

- MicroSD™/SD™ card port (not mandatory).
- At least one USB port available.
- No driver installation needed!

Software and user guides only available on www.irislink.com/start

Software suite for Windows®

- Microsoft® Windows® 10, 8, 7
- 512MB RAM (1GB recommended).
- 300MB of available hard disk space.

Software suite for Mac OS®

- Mac: OS X 10.10 or 10.9 and above (earlier versions not supported).
- Minimum 300MB of available hard disk space.
- 512MB RAM (1GB recommended).

State-of-the-art OCR software suite Readiris™ Pro & IRISCompressor™ Pro

- Convert any paper document, PDF, or image file into editable Office documents (Word, Excel®, Outlook®, Pages, Numbers and many others).
- Worldwide IRIS OCR for Windows & Mac including Asian & Arabic languages.
- Create hyper-compressed PDF files, ideal for indexing, archiving and sharing via email.



Document to Knowledge™
A CANON COMPANY

Canon
CANON GROUP

© Copyright 2016 IRIS s.a.
All rights reserved for all countries. IRIS, IRIS' product names, IRIS' logos and IRIS' product logos are IRIS trademarks. All other products and names mentioned are trademarks or registered trademarks from their respective owners.

