



Designation: 17627 LED Outdoor Sports 3AAA

Battery Requirement: 3 x AAA

Bulb required: 1pcs XPG2 R4 cool white, 5 Watt LED

Luminous intensity: High mode: 235 lumens or 5740 cd
Low mode: 60 lumens or 1350 cd

Range: 151 m High/73 m Low (calculated distance at intensity with an illuminance of 0.25lux).

Weight: 124.1g (without batteries).

Material: Aluminum
Silicon Rubber
TPE (Thermoplastic Elastomer)
All contact parts made of aluminium, bronze or nickel plated steel

Dimensions (mm):

A	122.2
B	39.7
C	30.6
D	28

Run Time: High: 8 hours (with VARTA HE)
Low: 35 hours (with VARTA HE)

Glow Ring Duration Time: 30mins (after 1hrs exposed under the powerful light)

Features: 2meters drop test
Super bright CREE cool white LED
MCU control push switch (High/Low/Off)
Photoluminescent material on head rubber
Type II anodized
Comfortable handle rubber grip
Lanyard
IPX4 water resistant
EN62471 eye safety risk group 1
10,000 Switch cycle life



No publication or circulation of data to third parties without consent of VARTA Consumer Batteries