

Data Sheet

LED Outdoor Sports 2AA

18628

A A

Designation: 18628 LED Outdoor Sports 2AA

Battery Requirement: 2x AA

Bulb required: 1pcs XPG2 R4 cool white, 5Watt LED

Luminous intensity: High: 235 lumens or 6500 cd

Low: 45 lumens or 1100 cd

Range: 160m High / 66m Low (calculated distance at maximum

luminous intensity with an illuminance of 0.25 lux)

Weight: 115.8g (without batteries)

Material: Aluminum

Silicon Rubber

TPE (Thermoplastic Elastomer)

All contact parts made of aluminium, bronze or

nickel plated steel

Dimensions (mm): A 160.4

B 36.6 C 24.2 D 20.1

Run Time: High: 4 hours (with VARTA HE)

Low: 30 hours (with VARTA HE)

Glow Ring Duration Time: 30mins (after 1hrs exposed under the

powerful light)

Features: 2meters drop test

Super bright CREE cool white LED

MCU control push switch (High/Low/Off)

Photoluminescent material on head rubber

Type II anodized

Comfortable handle rubber grip

Lanyard

IPX4 water resistant

EN62471 eye safety risk group 1

10,000 Switch cycle life

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

Phone: (+49) 7961/83-0, Fax: (+49) 800-827-8274