



Designation: 18629 LED Outdoor Sports 3C

Battery Requirement: 3xC size

Bulb required: 1pcs XPG2 R4 cool white, 5Watt LED

Luminous intensity: High: 310 lumens or 4980 cd
Low: 95 lumens or 2400 cd

Range: 141m High / 98m Low (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)

Weight: 312.7g (without batteries)

Material: Aluminum
Silicon Rubber
TPE (Thermoplastic Elastomer)
All contact parts made of aluminium, bronze or nickel plated steel

Dimensions (mm):

A	250.3
B	49.8
C	35.3
D	31.5

Run Time: High: 40 hours (with VARTA HE)
Low: 120 hours (with VARTA HE)

Glow Ring Duration Time: 30mins (after 1hrs exposed under the powerful light)



Features: 2meters drop test
Super bright CREE cool white LED
MCU control push switch (High/Low/Off)
Photoluminescent material on head rubber
Type II anodized
Comfortable handle rubber grip
Lanyard
IPX4 water resistant
EN62471 eye safety risk group 2
10,000 Switch cycle life

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries