

HSK cable glands for special applications

HSK-M-Flex

Metr. / Metr.-elongated



Material Nickel plated brass

Steel spring INOX 1.4310

Clamping insert Polyamide

Seal Buna-N


O-Ring Buna-N

Protection IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG)
within the specified clamping range

Operating Temperature -40 °C – 100 °C (-40 °F – 212 °F)

Advice:

- Other sealing material e.g. Silicone upon request



AG	Ø mm	GL mm	H mm	d mm	mm	Number	GL mm	Number long
M 12 x 1,5	3 – 6,5	6,5	55	6,8	14	1.623.1200.50	10	1.623.1200.30
M 12 x 1,5	2 – 5	6,5	55	6,8	14	1.623.1200.51	10	1.623.1200.31
M 16 x 1,5	4 – 8	6	66	8,2	19	1.623.1600.50	10	1.623.1600.30
M 16 x 1,5	2 – 6	6	66	8,2	19	1.623.1600.51	10	1.623.1600.31
M 16 x 1,5	5 – 10	6	77	10,3	20	1.623.1611.50	10	1.623.1611.30
M 16 x 1,5	3 – 7	6	77	10,3	20	1.623.1611.51	10	1.623.1611.31
M 20 x 1,5	6 – 12	6	88	12,3	22	1.623.2000.50	10	1.623.2000.30
M 20 x 1,5	5 – 9	6	88	12,3	22	1.623.2000.51	10	1.623.2000.31
M 20 x 1,5	10 – 14	6	98	14,3	24	1.623.2016.50	10	1.623.2016.30
M 20 x 1,5	7 – 12	6	98	14,3	24	1.623.2016.51	10	1.623.2016.31
M 25 x 1,5	13 – 18	7	111	18,4	30	1.623.2500.50	12	1.623.2500.30
M 25 x 1,5	9 – 16	7	111	18,4	30	1.623.2500.51	12	1.623.2500.31