


Coaxial Cable Connector 14_BMA-50-2-2/111_N

Description

Straight bulkhead cable plug

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0035 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	
Washer	Bronze	

Related Documents

Catalogue drawing	DCA-00009614
Assembly instruction	DOC-0000180997
Mounting hole	DOU-00008972

Ordering Information

Single package	14_BMA-50-2-2/111_NE
----------------	----------------------

Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------