

Coaxial Cable Connector 16_N-50-7-26/133_N

Description

Right angle cable plug

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0647 kg

Environmental Data

Operating temperature 2011/65/EC, RoHS	-65 °C to 165 °C compliant
---	-------------------------------

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00007180
Catalogue drawing	DOU-00007182
Assembly instruction	DOC-0000179896

Ordering Information

Single package	16_N-50-7-26/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_213_U, GX_07272, RG_214_U
-----------------	------------------------------