

Within Series Adaptor 34_SMA-50-0-100/111_N

Description

Bulkhead adaptor jack/jack
SMA-26.5GHz jack (female) / SMA-26.5GHz jack (female)

For Test & Measurement applications
Expanded freq. range up to 26.5 GHz

Interface standard
Series SMA-26.5GHz - SUHNER-SMA-26.5GHz



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	26.5 GHz
VSWR	DC - 26.5 GHz ≤ 1.05 + 0.014 f (GHz)
Electrical length	25.72 mm

Mechanical Data

Number of matings	500
Weight	0.0041 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - SMA-26.5GHz jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Interface - SMA-26.5GHz jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013642
Mounting hole	DOU-00008731

Ordering Information

Single package	34_SMA-50-0-100/111_NE
----------------	------------------------