


## Coaxial Cable Connector 16\_TNC-50-3-13/133\_N

### Description

Right angle cable plug

Interface standards

IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 11 GHz

#### Mechanical Data

Centre contact crimped  
Outer 2contact crimped  
Weight 0.0301 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

### Related Documents

Outline drawing DOU-00008246  
Catalogue drawing DOU-00005944  
Assembly instruction DOC-0000335265

### Ordering Information

Single package 16\_TNC-50-3-13/133\_NE

### Additional Information

Suitable cables RG\_58\_C/U, S\_03232, RG\_141\_A/U-03