

Coaxial Cable Connector 11_MMCX-50-1-1/111_O

Description

Straight cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0009 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	

Related Documents

Outline drawing	DOU-00006970
Catalogue drawing	DOU-00006168
Assembly instruction	DOC-0000179110

Ordering Information

Bulk 100 pcs package	11_MMCX-50-1-1/111_OH
Single package	11_MMCX-50-1-1/111_OE

Additional Information

Suitable cables	RG_178_B/U, RG_196_A/U, RG_196_A/U
-----------------	------------------------------------