

## Coaxial Cable Connector 11\_TNC-50-7-2/133\_N

### Description

Straight cable plug

Interface standards

IEC 60169-17\_MIL-STD-348A/313\_CECC 22200



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0397 kg

#### Environmental Data

Operating temperature 2011/65/EC, RoHS	-65 °C to 165 °C compliant
---	-------------------------------

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00008068
Catalogue drawing	DOU-00008070
Assembly instruction	DOC-0000179854

### Ordering Information

Single package	11_TNC-50-7-2/133_NE
----------------	----------------------

### Additional Information

Suitable cables	RG_213_/U, RG_214_/U, RG_393_/U
-----------------	---------------------------------