

Coaxial Cable Connector 24_QN-50-3-3/13-_N

Description

Straight bulkhead cable feed through

Interface standards

QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 3 GHz	3 to 6 GHz
Return loss	40 dB	35 dB	25 dB

Mechanical Data

Centre contact	plugged
Outer 2contact	soldered
Weight	0.0188 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) / SUCOPRO Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	
Washer	Bronze	

Related Documents

Outline drawing	DOU-00009880
Catalogue drawing	DCA-00009882
Assembly instruction	DOC-0000186844
Mounting hole	DOU-00008737

Ordering Information

Single package	24_QN-50-3-3/13-_NE
----------------	---------------------

Additional Information

Suitable cables	SUCOFORM_141, EZ_141_AL_TP_M17, MULTIFLEX_141
-----------------	---