

Within Series Adaptor 31_N-50-0-2/133_N

Description

Adaptor jack/jack
N jack (female) / N jack (female)

Interface standard
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	18 GHz		
Frequency range	DC to 2 GHz	2 to 8 GHz	8 to 12.4 GHz
Return loss	≥ 30 dB	≥ 15 dB	≥ 10 dB

Mechanical Data

Number of matings	500
Weight	0.0411 kg

Environmental Data

Operating temperature 2002/95/EC (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Catalogue drawing	DCA-00013814
-------------------	--------------

Ordering Information

Single package	31_N-50-0-2/133_NE
----------------	--------------------