

Coaxial Cable Connector 16_QLA-01-2-1/122_N

Description

Right angle cable plug

Interface standards
NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0051 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	

Related Documents

Catalogue drawing	DOU-00006830
Assembly instruction	DOC-0000179948

Ordering Information

Single package	16_QLA-01-2-1/122_NE
----------------	----------------------

Additional Information

Suitable cables	RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U
-----------------	--