

Easy IP-Cam HD wireless TX-55

Wireless Security Camera HD powered by batteries for indoor and outdoor use



- Ideal for monitoring indoor & outdoor locations, like rooms, garage, garden & areas difficult to view
- No power connection required, working with batteries
- Standby time ~3–5 months (with 1–3 events/day)
- Push notification via the APP when motion is detected
- Video resolution HD 1280 x 720 (720P) @ 30fps max.
- 1MP CMOS image sensor
- IR LED for clear night shots
- Motion detection ~5–6m by PIR-Sensor with ~1–1.5 seconds triggering time
- Easy to attach via magnet, 3M adhesive stripe or screws
- Free iOS & Android APP for live monitoring playback
- Built-in microphone for audio recordings
- IPX4 protection class (splashproof)

Technical Specifications:

- Image sensor 1/4" CMOS OV9712, 1 megapixel
- Lens: F/NO=2.4, f=2.45mm, 120° viewing angle, fixed focus
- Depth of field ~50cm to infinity
- White Balance / Exposure: Automatically
- Built-in WiFi module IEEE 802.11b/g/n, ~20–30m distance
- Video encoder H.264 / Video file format MP4
- Picture resolution 1280x800 / Picture format JPG
- Audio encoder AAC & AC3 mono / Audio input sample rate 48K & MIC
- Storage: MicroSD card up to 32GB
- Power supply: 4x CR123A batteries* (*included)
- Weight / Dimensions: 150.5g (without batteries) / (L) 11.2 x (W) 6.5 x (H) 7.4cm (with stand)

Package Contents:

- Easy IP-Cam HD wireless TX-55
- Camera chassis
- 4x screws & 3M adhesive stripe
- Powerful magnet with iron plate
- 4x CR123A batteries
- User Manual



4 260358 121369
Black / Article-No. 4575



4 260358 122427
White / Article-No. 4612