

WiFi IP-Cam Dome PRO FullHD Outdoor TX-66

IP-Dome Camera with 1080P & wireless transmission for outdoor use





 FullHD 1080P Video Resolution / FullHD 1080P Videoauflösung	 CMOS Image Sensor 3MP / CMOS Bildsensor 3MP	 WiFi Transmission / WiFi Übertragung	 Live Surveillance / Live-Überwachung
 Free iOS & Android APP / Freie iOS & Android APP	 Motion Detection / Bewegungserkennung	 IR-LED Function / IR-LED Funktion	 MicroSD Card Storage / MicroSD Kartenspeicherung
 High Quality Metal Housing / Hochwertiges Metallgehäuse	 Viewing Angle 77° / Betrachtungswinkel 77°	 Waterproof IP67 / Wasserfest IP67	 Shockproof IK10 / Stoßfest IK10



- Ideal for monitoring outdoor & indoor areas
- FullHD video resolution 1080P with 25/30fps
- Supports WiFi up to ~50m open areas
- Live surveillance via free iOS & Android APP
- Day & Night surveillance (Auto-ICR, Colour, B/W)
- Motion detection
- H.264 & MJPEG dual-stream encoding
- Data storage on MicroSD cards up to 128GB
- Monitoring options: APP (Technaxx My Secure Pro) & PC (via Internet)
- Worldwide access via Smartphone, PC/Notebook, Tablet PC, etc.
- Protection class IP67 (dustproof & waterproof) & IK10 (shockproof)
- High quality metal housing

Technical Specifications:

- 1/3" 3MP progressive scan CMOS sensor
- Effective pixel 2304 horizontal x 1536 vertical
- Lens: 3.6mm fixed with viewing angle 77° horizontal
- Min. illumination: 0.1Lux@F2.0 (colour), 0Lux@F2.0 (IR on)
- Video compression: H.264 / H.264H / H.264B / MJPEG
- Video resolution: 1080P(1920x1080)@25/30fps & 3M(2304x1296)@20fps & 720P(1280x720) & VGA(640x480)/QVGA(320x240)@25/30fps
- Video bit rate: H.264: 32Kbps~8192Kbps
- IR LED distance ~30m maximum
- SNR: more than 50dB
- Ethernet: RJ-45 (10/100Base-T)
- WiFi (IEEE802.11b/g/n), ~50m open areas
- Power supply / consumption: DC 12V / <5.5W (IR on)
- Working temperatures: -30°C~+50°C, less than 95% relative humidity
- Weight / Dimensions: 450g / Ø 11.0 x (H) 8.1 cm

Package Contents:

- WiFi IP-Cam Dome PRO FullHD outdoor TX-66
- Power Adapter
- Antenna
- Screws
- CD
- User Manual



Article-No. 4609

