

Security Premium Surveillance Camera Set TX-29

10.1 inch monitor with recording function & HD outdoor camera



- | | | | |
|---|--|--|--|
| 10.1" HD LCD Monitor with loudspeaker / 10.1" HD LCD Monitor mit Lautsprecher | HD Camera 720P with CMOS Sensor / HD Kamera 720P mit CMOS Sensor | Wireless Transmission with 2.4GHz / Funkübertragung mit 2.4GHz | Wireless Camera Connection max. 4 Cameras / Kabellose Kameraverbindung max. 4 Kameras |
| USB Backup Function / USB-Backup-Funktion | Real Time Video Recording / Echtzeit-Videoaufnahme | Hard Disk Storage Function / Festplattenspeicherfunktion | Push Message via APP when motion is detected / Push-Nachricht via APP bei Bewegungserkennung |
| PIR Day & Night Vision Function / PIR-Tag- & Nachtsichtfunktion | 4-Windows Split-Screen Function / 4-Fenster-Teilungsfunktion | IP66 Waterjet & Dust Protection / IP66 Strahlwasser- & Staubschutz | Built-in Microphone for Audio Recording / Eingebautes Mikrofon für Audioaufnahmen |



- Recorder & Receiver & Monitor in one device
- Wireless transmission with 2.4GHz via Plug & Play
- HD LCD monitor with loudspeaker
- HD camera video resolution 1280x720 (720P)
- Built-in camera microphone for audio recording
- PIR sensor with ~8m distance at day & night
- Push message via APP when motion is detected
- Wireless camera connection with up to 4 cameras
- 4-windows split-screen function with real-time/routine/event surveillance
- Hard disk storage function & USB backup function
- Network operation via LAN cable connection
- Mobile viewing via free iOS & Android APP (Technaxx Security Premium)
- Easy monitoring via PC (PC Client software)
- Worldwide PC access (DDNS) [www.technaxxp2p.de]
- IP66 camera protection class against waterjet & dust

Technical Specifications Monitor:

- Supports Wireless/IP camera video input
- SATA hard disk connection up to 4TB HDD (2.5")
- Video capture mode: manual, time, motion, PIR
- HD LCD monitor with loudspeaker
- H.264 dual-stream video compression (main & extra stream)
- Video resolution D1/720P
- AV input 4 channels maximum
- AV output: 1 channel HDMI video output
- 2 USB2.0 ports (backup & mouse)
- Network interface: 1x RJ45 10Mbit/s / 100Mbit/s, 1x WiFi interface for cameras
- Automatic connection via DHCP (Dynamic Host Configuration Protocol)
- Protocol: UPnP, SMTP (only SSL), PPPoE, DHCP, DDNS
- Power supply: DC 12V/2A
- Power consumption ≤ 15W (without HDD)
- Operating conditions: -10°C~+55°C, humidity 10%~90% RH
- Mounting possibilities: Stand & Wall bracket
- Weight / Dimensions: 1kg (without HDD* & stand) / (L) 25.0 x (W) 3.6 x (H) 16.6cm [*HDD not included]

Technical Specifications outdoor Camera:

- Image sensor 1/4" CMOS with 1 megapixel
- Video resolution HD 1280x720 (720P)
- WiFi transmission up to ~50m open areas
- Camera repeater function to enlarge WiFi distance up to ~150m
- Motion detection ~10m (day/night)
- PIR sensor ~8m (day/night); 120° horizontal & 60° vertical
- 1 infra red Array LED for night vision mode (~15m) & IR-Cut
- Lens: f=4mm; shutter 1/25s to 1/25000s; fixed focus
- Viewing angle 57.4° horizontal & 42.8° vertical
- Min. illumination: Colour 0.1 Lux, B/W 0.01 Lux, Auto, Auto 3D-DNR
- Protocol: RJ45, WiFi 802.11b/g/n
- Power supply: DC 12V/1A
- Power consumption ≤ 6W
- IP66 protection class (waterjet & dust proof)
- Operating conditions: -10°C~+50°C, humidity 30%~80% RH
- Weight / Dimensions: 550g / (L) 15.0 x (W) 9.7 x (H) 8.7cm

Package Contents:

Monitor with Stand, AC/DC Adapter 12V/2A, Wall bracket & screws & dowels, HDD bracket & screws, Antenna

Outdoor Camera with AC/DC Adapter 12V/1A, Wall bracket & screws & dowels, Antenna, Waterproof end cap

General: USB Mouse, Network Cable (2m), CD, User Manual, [*HDD not included]

Additional accessory:

Additional Camera for Security Premium Surveillance Camera Set TX-29 & TX-30 (and AC/DC adapter 12V/1A, wall bracket & screws & dowels, antenna, waterproof end cap)
EAN Code: 4260101737656, Article-No. 4664



Article-No. 4641

