

# Temperature and Humidity Sensor – indoor

Product ref.: 150181A0



## Product features

- Measuring of indoor temperature and humidity
- Regulates the room temperature in connection with one or more Homematic IP Radiator Thermostats or Homematic IP Floor Heating Actuators
- Particularly user-friendly and immediately ready for use thanks to radio communication
- Simple and flexible installation thanks to supplied adhesive strips or screws
- Integration into multi-gang frames or 55 mm frames of other manufacturers (Berker, ELSO, Gira, merten, JUNG)
- Can be used with the Home Control Access Point in connection with the Homematic IP app, the Homematic Central Control Unit CCU2 as well as with various partner solutions

## Technical specifications

Supply voltage	2x 1.5 V LR03/micro/AAA
Current consumption	20 mA max.
Battery life	2 years (typ.)
Degree of protection	IP20
Ambient temperature	5 to 35 °C
Dimensions (W x H x D)	Without frame: 55 x 55 x 19 mm Incl. frame: 86 x 86 x 20 mm
Weight	85 g (including batteries)
Radio frequency	868.3 MHz/869.525 MHz
Typ. open area RF range	130 m

## Logistical data

Product reference	150181A0
EAN code	4047976501816
Short description	HmIP-STH
Packing unit	90
Packing dimensions	122 x 112 x 48 mm

## Package contents

Homematic IP Temperature and Humidity Sensor – indoor

Clip-on frame

Mounting plate

Double-sided adhesive strips (2x)

Screws 3.0 x 30 mm (2x) and plugs 5 mm (2x)

1.5 V LR03/micro/AAA batteries (2x)

User manual