

7" LCD DISPLAY

Capacitive touch TFT display



The 7 inch TFT display expands the Raspberry Pi or the Banana Pi with a touchscreen display in no time. It can also be used on any desktop computer and convinces with its high contrast and color-fast display. With a maximum resolution of 1024 x 600 pixels, this display is suitable for any application.

HAUPTMERKMALE

Model	7" LCD Display
Resolution	1024x600
LCD Type	TFT
Maximum brightness	300 cd/m ²
Connections	HDMI, Micro-USB
Touch controller	GT811
Touch screen technology	Capacitive touch screen, PC: supports 5-point touch, Raspberry Pi: single touch
Backlight	LED
Operating temperature	0 °C - 70 °C
Viewing angle	up to 85 °
Supported devices	Raspberry Pi A+, B+, 2B, 3B, 3B+, 4B Banana Pi, Banana Pro Windows PCs

ADDITIONAL DETAILS

Dimensions	154,21 x 85,92 mm
Weight	242 g
Items shipped	Display
EAN	4250236814995
Customs tariff no.	8473302000