

# **LED flush-mounted double-dimmer**

## with central plate T42.07

## as ready-to-install device T42.07.01

#### Item-no.:

4260x0700 (central plate white, similar to RAL9010) 4290x0700 (central plate white, similar to RAL9016) 4210x0700 (central plate white, similar to RAL9003)

#### Item-no.:

4260x0701 (ready-to-install device white similar to RAL9010) 4290x0701 (ready-to-install device white similar to RAL9016)





To use in exchange for series switches and to dim two illuminants in a space saving way

Suitable for dimmable LED lamps, 230V-incandescent-, halogen and, NV-halogen lamps with mag. transformer

Fits in common flush-mounted switch boxes with an installation opening of 60 mm according to DIN 49073

With central plate 50x50 mm or as ready-to-install device including frame and central plate

Available in three shades of white – similar to RAL9010, similar to RAL9016 and similar to RAL9003

Short-circuit/overload protection through fine wire fuse

EHMANN advantage - 100% quality checks, 5-year warranty, German manufacturer





EHMANN Service - LED recommendation list









# LED flush-mounted double-dimmer with central plate T42.07 or as ready-to-install device T42.07.01

### Technical data

2x 15 - 110 W/VA	2x 5 - 40 W	230 V ~ (+/- 10%) / 50 Hz
Power	LED Power	Rated voltage

Suitable for dimmable LED lamps, 230V-incandescent-, halogen and, NV-halogen lamps with mag. transformer

Operation principle: Leading edge

Operation: Rotary knob with turn-off switch

Shaft: Ø 4 mm plastic

Connection: Screw terminal up to 2 x 2,5 mm<sup>2</sup> (rigid)

Over-temperature protection: Thermal fuse

Short-circuit/overload protection: Fine wire fuse T1AH/250V

(incl. spare fuse)

















### LED recommendation list

"Which LED lamp works ideal with this LED dimmer". Via QR Code or www.ehmann-gmbh.de



Item-no. 4260x0700 (with cp)	EAN 401209600682 4	PU 10
ltem-no. 4260x0701 (ready)	EAN 4012096006831	PU 10
ltem-no. 4290x0700 (with cp)	EAN 401209600679 4	PU 10
ltem-no. 4290x0701 (ready)	EAN 401209600680 0	PU 10
Item-no. 4210x0700 (with cp)	EAN 4012096006817	PU 10

71 x 71 x 33 mm Dimensions (L x W x H) (without cover)