

Kodak PIXPRO

Digital Cameras

ASTRO ZOOM AZ252



FEATURES:

Discover the new collection of KODAK PIXPRO Digital Cameras and discover a world of creativity at your fingertips. The AZ252 is the perfect bridge camera to explore your love of photography. Ample mega pixels, 25X optical mega zoom and a wider angle lens than traditional models, this camera could easily become your new best friend. KODAK PIXPRO Digital Cameras – Tell your story.

- 25X Optical Zoom
- 720p HD Video
- 16MP
- 24mm Wide Angle
- OIS (Optical Image Stabilization)
- 3" LCD
- AA Battery



Images are simulated.

Available Colors:

25X
OPTICAL
ZOOM

24mm
WIDE

16MP

3"
7.6CM

HD

Panorama
Capture

Kodak

PIXPRO AZ252

Digital Camera

25X
OPTICAL
ZOOM

24mm
WIDE

16MP

3"
7.6cm

HD

Panorama
Capture

SPECIFICATIONS

AZ252

Effective Image Sensor Pixels	16.15 Megapixels
Total Image Sensor Pixels	16.44 Megapixels [1/2.3" CCD]
Lens	
Focal Length [35mm film equivalent]	4.3 mm (Wide) — 107.5 mm (Tele) [24 mm (Wide) — 600 mm (Tele)]
F number	F3.7 (Wide) — F6.2 (Tele)
Lens Construction	11 groups 12 elements
Optical Zoom	25x
Focusing Range	Normal: (Wide) 60 cm — ∞, (Tele) 250 cm — ∞ Macro: 3 cm — ∞ (Wide Only)
Anti-Shake	OIS (Optical Image Stabilization)
Digital Zoom	4x Digital Zoom (Combined Zoom: 100x)
Number of Recording Pixels Still Image	(4:3) 16MP: 4608x3456, 10MP: 3648x2736, 5MP: 2592x1944, 3MP: 2048x1536, 0.3MP: 640x480, (3:2) 14MP: 4608x3072, (16:9) 12MP: 4608x2592, 2MP: 1920x1080
Movie	1280x720(30/15fps), 640x480(30fps), 320x240(30fps)
Image Compression	Best, Fine, Normal
DCF, DPOF (Ver1.1) Support	Yes
File Format	
Still Image	Exif 2.3 (JPEG)
Movie	Movie Format: MOV (H.264), Audio: G.711 [Monaural]
Shooting Modes	Auto, P, S, A, M, Face Beautifier, Panorama
SCN Modes	ASCN, Sport, Beach, Sunset, Fireworks, Night Landscape, Sketch, Snow, Children, ID, Glass, Photo Frame, Panning Shot, Portrait, Fish Eye, Party, Indoor, Leaf, Museum, Night Portrait, Pet (Dog), Pet (Cat), Movie, CS, Landscape
Detection Features	Face, Smile, Blink, Cat, Dog
Photo Touch-up	Red-Eye Reduction, Skin Soften, Eye Brightening, Eye Enlargement, HDR
Panorama	0° - 180°
LCD Display	3.0 inch (230K Pixels)
ISO Sensitivity	Auto, ISO 80/100/200/400/800/1600/3200 (4M)
AF Method	Single AF, Multi-AF (TTL 9-point), Object Tracking, Face Detection
Exposure Metering Method	Artificial Intelligence AE (AiAE), Center-Weighted Average, Spot (Fixed to Center of Frame), Face AE
Exposure Control Method	Program AE (AE-Lock Available), Shutter Prior AE
Exposure Compensation	+/- 2EV in 1/3 Step Increments
Shutter Speed	1/2000 - 30 Seconds
Continuous Shooting	Yes
Playback Modes	Single Photo, Index (9/16 Thumbnails) Slide Show, Date, Zoom (Approx. x2 - x8)
White Balance Control	Auto (AWB), Daylight, Cloudy, Flourescent, Flourescent CWF, Incandescent, Manual, Color Temperature Setting (1900K - 10000K)
Flash	
Flash Method	Pop-up (Manual)
Flash Modes	Auto, Red-Eye Reduction, Forced Flash, Slow Synchro, Red-Eye Reduction + Slow Synchro
Shooting Range	(Wide) Approx. 0.5 m - 7.1 m (ISO800); (Tele) Approx. 1.2 m - 4.2 m (ISO800)
Recording Media	Internal Memory: Approx. 8MB SD/SDHC Card (Up to 32GB Support) [MMC Card not supported]
Other Features	Eye-Fi, PictBridge, ExifPrint Support, Multi-Language Support (27 Languages)
Jacks	AV-OUT/USB 2.0 (Micro 5 pin USB), HDMI (Type D)
Power	AA Alkaline Battery (x4) AA NiMH Battery (x4) (Not Included)
Shooting Capability (Battery Performance)	Approx. 280 Shots of Alkaline Battery (Based on CIPA Standards) Approx. 500 Shots of AA NiMH Battery (Based on CIPA Standards)
Operation Environment	Temperature: 32° - 104°F / 0° - 40°C, Humidity: 0 - 90%
Dimensions (WxHxD)	Approx. 4.47 x 3.06 x 2.74 in. / 113.6 x 77.7 x 69.7 mm (Based on CIPA Standards)
Weight	Approx. 12.5 oz. / 336g (Body Only)
Supplied Accessories	AA Alkaline Battery(x4), USB Cable, Neck Strap, Lens Cover, Quick Start Guide, Warranty Card, Service Card

JK Imaging Ltd.

JK Imaging Ltd.
17239 South Main Street
Gardena, CA 90248

To learn more about KODAK PIXPRO Digital Cameras:
visit: kodakpixpro.com

