


TECHNICAL DATA

PRODUCT : Polyimid Folie 300 x 270 mm

一, PRODUCT STRUCTURE



二.PERFORMACE INDEX

NO	INDEX NAME	UNIT	INDEX VALUES	TEST METHOD
1	Backing Thickness	mm	0.125	GB/T 7125-1999
2	Dry Coating Thickness	mm	0.035	GB/T 7125-1999
3	Total Thickness	mm	0.16	GB/T 7125-1999
4	PET Fluorine Liner Thickness	mm	0.075	GB/T 7125-1999
5	Voltage Resistance	KV	≥5	GB/T 7752-1987
6	Insulation Resistance	Ω	1.0*10 ¹³	GB/T 1410-2006
7	Tensile Strength	KG/25mm	14	GB/T 7753-1987
8	Elongation Break	%	0.65	GB/T 7753-1987
9	Pcel Adhesion	N/25mm	3~8	GB/T 2792-1998
10	Hea Resistance	℃ ³	250℃/1h不残胶	GB/T 17875-1999
11	Color	----	Dark Brown	