

KERN HCB1T-3

Die Handlichen für erhöhte Lasten bis 1 Tonne!

KERN[®]



Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 4 kg |
| Precision (of [Max]): | 0,005 |
| Readout [d]: | 2 kg |
| Recommended adjusting weight: | 500 kg (M1) |
| Reproducibility: | 2 kg |
| Resolution: | 500 |
| Stabilisation time: | 2 s |
| Warm up time: | 10 min |
| Weighing range [Max]: | 1 t |
| Weighing system: | Strain gauge |
| Weighing units: | kg lb N |

Display

| | |
|-----------------------|----------|
| Display digit height: | 1,200 cm |
|-----------------------|----------|

Functions

| | |
|---------------------|-----|
| Data hold function: | yes |
|---------------------|-----|

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 5 °C |

Power supply

| | |
|-----------------|-------|
| Operating time: | 300 h |
|-----------------|-------|

Service

Adjustment at the location of installation: 961-250

| | |
|--------------------|----------|
| DAkkS Certificate: | 963-130H |
|--------------------|----------|

Category

| | |
|----------------|---------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Hanging scale |

Packaging & shipping

| | |
|-------------------------------|-------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 215 x 150 x 85 mm |
| Gross weight: | 880 g |
| Net weight: | 520 g |
| Shipping method: | Parcel service |

Construction

| | |
|-----------------------------|------------------|
| Casing material: | Plastic |
| Dimensions housing (WxDxH): | 80 x 48 x 150 mm |