

# KERN MTA 400K-1M



Stabile Stehhilfewaage für ein sicheres Gefühl beim Wiegen â mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik



Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	100 g   200 g

## Functions

BMI function:	yes
Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	5 %

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	20 h
Operating time (Backlight off):	40 h
Operating time (Backlight on):	20 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

Adjustment at the location of installation: 961-250

DAkkS Certificate:	963-130
Verification:	965-130

## Category

Brand:	KERN
Category:	Balances
Product Group:	Handrail scale

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	900 x 876 x 1375 mm
Gross weight:	65 kg
Net weight:	49 kg
Shipping method:	Freight forwarder

## Measuring system

Adjustment options:	External calibration
Linearity:	100 g   200 g
Readout [d]:	100 g   200 g
Recommended adjusting weight:	400 kg (M1)
Reproducibility:	100 g   200 g
Resolution:	3 2.000
Tare range:	-399800000 mg
Warm up time:	10 min   10 min
Weighing range [Max]:	300 kg   400 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	2,500 cm
Display digit height:	5 mm

## Technical data about verification

Minimum load [Min]:	2 kg   4 kg
Periodic Verification for Italy:	969-112
Verification approval conforming	yes

# KERN MTA 400K-1M



Stabile Stehhilfewaage für ein sicheres Gefühl beim Wiegen â mit Eich- und Medizinzulassung für den professionellen Einsatz in der medizinischen Diagnostik

## Construction

Casing material:	Steel lacquered
Dimensions of display device (WxDxH):	200 x 55 x 128 mm
Dimensions of weighing plate (WxDxH):	780 x 680 x 68 mm
of stand:	94 cm
Level indicator:	yes
Material weighing plate:	Plastic
Overall dimensions mounted (WxDxH):	780 x 680 x 1100 mm
Weighing surface (WxD):	600 x 600 mm