

KERN 287-106

Mechanische Gewichts- und Kraftmessung mit Qualitätsfeder für lange Lebensdauer



Measuring system

Precision (of [Max]):	0,003
Readout [d]:	1 g
Resolution:	100
Warm up time:	10 min
Weighing range [Max]:	100 g

Service

Adjustment at the location of installation: 961-247

ISO calibration certificate: 961-100

Category

Category:	Balances
Product Group:	Spring scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	230 x 26 x 17 mm
Gross weight:	39 g
Net weight:	25 g
Shipping method:	Parcel service