

KERN 289-104

Mechanische Gewichts- und Kraftmessung mit Qualitätsfeder für lange Lebensdauer



Measuring system

Measuring range [Max]:	10 N
Precision (of [Max]):	0,003
Readout [d]:	0,100 N 0,500 N

Service

ISO Calibration certificate (Tensile):	961-1610
--	----------

Category

Category:	Force gauges
Product Group:	Mechanical force gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	230 x 26 x 17 mm
Gross weight:	39 g
Net weight:	25 g
Shipping method:	Parcel service