


KERN BIC 1T-4

KERN

High-resolution floor scale with 2×3000 [d] and the best price-to performance ratio



Category

Brand	KERN
Product category	Industrial scale
Product group	Floor scale
Product family	BIC

Measuring System

Weighing system	Strain gauge
Number of weighing ranges	2
Weighing capacity [Max]	600 kg; 1500 kg
Readability [d]	0,2 kg; 0,5 kg
Reproducibility	0,2 kg; 0,5 kg
Linearity	± 0,6 kg; 1,5 kg
Resolution	3.000, 3.000
Tare range	-1500 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1500 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	1 kg; 2,5 kg
Load cell connection	4-wire
Construction type of the scale	Multi-range balance
Units	kg lb
Maximum creep (15 minutes)	2 kg
Maximum creep (30 minutes)	4 kg
Default unit	kg
Loadcell type	KELI SQB

Display

Display type	LCD
Display type	LCD

Display backlight	✓
Display digit height	25 mm

Construction

Dimension (W×D×H)	1200×1500×108 mm
Dimension display device (W×D×H)	235×114×51 mm
Dimensions weighing surface (W×D)	1200×1500 mm
Dimensions weighing surface	1200×1500 mm
Dimensions weighing platform (W×D×H)	1200×1500×108 mm
Material	steel, lacquered
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Material display housing	plastic
Material load cell(s)	steel
Level indicator	✓
Levelling feet adjustable	✓
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	15 m
Platform Construction	Chequer plate, welded
Load cells - number	4

Functions

Underfloor weighing	None
Hold function	✓
IP protection - platform	IP67
IP protection - load cell	IP67
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (single)
Number of keys for operation	4

Power Supply

Supplied power supply	Power supply & battery function (battery not included)
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US

KERN BIC 1T-4



High-resolution floor scale with 2×3000 [d] and the best price-to performance ratio

Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0,3 A
Input voltage device / power [Max]	9 V, 100 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø outside 5,5 mm, Ø inside 2,5 mm, long 10 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	60 h
Battery/Accu connected	not connected, enclosed

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for DAkkS calibration	963-130
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	1270×1560×240 mm
Shipping method	Freight
Net weight approx.	150 kg
Gross weight approx.	170 kg
Shipping weight	167 kg

Product information

GTIN/EAN number	4045761193178
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

