

# KERN CKE360-3

Selbsterklärende Zählwaage mit Laborgenauigkeit, Zählauflösung bis zu 360.000 Punkte



## Measuring system

Adjustment options:	External calibration
Linearity:	5 mg
Readout [d]:	1 mg
Recommended adjusting weight:	200 g (F1); 100 g (F1)
Reproducibility:	1 mg
Resolution:	360000
Stabilisation time:	3 s
Tare range:	360 g
Warm up time:	2 h
Weighing range [Max]:	360 g
Weighing system:	Strain gauge
Weighing units:	g

## Display

Display digit height:	9 mm
-----------------------	------

## Counting

Counting resolution:	360000
Minimum piece weight at piece counting (Laboratory):	1 mg
Minimum piece weight at piece counting (Normal):	10 mg

## Functions

Counting function:	yes
Suspended weighing:	Hook

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	10 °C

## Power supply

Charging time:	10 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h
Rechargeable battery:	Rchrg. battery optional

## Service

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	360 x 230 x 180 mm
Gross weight:	2,200 kg
Net weight:	1 kg
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	Plastic
Dimensions draft shield (ÅxH):	106   42
Dimensions housing (WxDxH):	167 x 250 x 85 mm
Level indicator:	yes
Material weighing plate:	plastic
Overall dimensions mounted (WxDxH):	167 x 250 x 123 mm
Revolving screw feet:	yes
Weighing space (ÅxH):	90   40
Weighing surface (d):	81