

# KERN DB 1-4

Komfortable Drehmoment-Prüfung von Werkzeugen



## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	350 x 295 x 30 mm
Gross weight:	3,770 kg
Net weight:	1 g
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	Metal lacquered
Dimensions housing (WxDxH):	200 x 100 x 50 mm

## Measuring system

Measuring range [Max]:	1 Nm
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,005
Readout [d]:	0 Nm
Weighing units:	Nm. kgf/cm. kgf/m. in/lbs. ft/lbs

## Functions

Function to set limits:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

## Power supply

Charging time:	14 h
Input voltage:	100 V - 240 V
n/a:	EURO

n/a:	Mains adapter external
------	------------------------

## Service

ISO calibration certificate:	961-120
------------------------------	---------

## Category

Brand:	Sauter
Category:	Torque