

KERN DB20-3

Komfortable Drehmoment-Prüfung von Werkzeugen



Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	350 x 295 x 30 mm
Gross weight:	2 g
Net weight:	1 g
Shipping method:	Parcel service
UN number:	3496

Construction

Casing material:	Metal lacquered
Dimensions housing (WxDxH):	200 x 100 x 50 mm

Measuring system

Measuring range [Max]:	20 Nm
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,005
Readout [d]:	0,005 Nm
Weighing units:	Nm. kgf/cm. kgf/m. in/lbs. ft/lbs

Functions

Function to set limits:	yes
Peak function:	yes

Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

Power supply

Charging time:	14 h
Input voltage:	100 V - 240 V
n/a:	EURO

n/a:	Mains adapter external
------	------------------------

Service

ISO calibration certificate:	961-120
------------------------------	---------

Category

Brand:	Sauter
Category:	Torque