

KERN EOC100K-2XXL

Allround-Paketwaage mit praktischem Flip/Flop-Auswertegerät für optimale Bedienbarkeit



Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 60 g 150 g |
| Readout [d]: | 20 g 50 g |
| Recommended adjusting weight: | 150 kg (M1) |
| Reproducibility: | 20 g 50 g |
| Resolution: | 3 3.000 |
| Stabilisation time: | 2 s |
| Tare range: | -150000000 mg |
| Warm up time: | 10 min 10 min |
| Weighing range [Max]: | 60 kg 150 kg |
| Weighing system: | Strain gauge |
| Weighing units: | g kg lb oz |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,400 cm |
|-----------------------|----------|

Counting

| | |
|--|-------|
| Counting resolution: | 15000 |
| Minimum piece weight at piece counting (Laboratory): | 10 g |
| Minimum piece weight at piece counting (Normal): | 100 g |

Functions

| | |
|--|-----|
| Counting function: | yes |
| Function to save totals: | yes |
| Percentage determination: | yes |
| Vibration-free weighing (Animal weighing program): | yes |
| Weighing with tolerance range: | yes |

Environmental conditions

| | |
|--------------------------------|--------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | -10 °C |
| Minimum humidity: | 0 % |

Power supply

| | |
|----------------|----------------|
| Charging time: | 12 h |
| Input voltage: | 100V-240V 0.4A |
| n/a: | CH EURO UK US |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|---------------------------------|----------------------------------|
| Operating time (Backlight off): | 35 h |
| Operating time (Backlight on): | 8 h |
| Rechargeable battery: | Rchrg. battery optional - intern |

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

| | |
|----------------|------------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Industrial scale |

Packaging & shipping

| | |
|-------------------------------|----------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 1015 x 282,5 x 85 mm |
| Gross weight: | 20 kg |
| Net weight: | 15,700 kg |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|-------------------|
| Cable length of display device: | 2,700 m |
| Dimensions of display device (WxDxH): | 268 x 115 x 80 mm |
| Dimensions of weighing plate (WxDxH): | 950 x 500 x 60 mm |
| of stand: | 33 cm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Revolving screw feet: | yes |
| Wall mount: | yes |
| Weighing surface (WxD): | 950 x 550 mm |