

KERN EOC60K-2L

Allround-Paketwaage mit praktischem Flip/Flop-Auswertegerät für optimale Bedienbarkeit



Measuring system

Adjustment options:	External calibration
Linearity:	30 g 60 g
Readout [d]:	10 g 20 g
Recommended adjusting weight:	60 kg (M1)
Reproducibility:	10 g 20 g
Resolution:	3 3.000
Stabilisation time:	2 s
Tare range:	-60000000 mg
Warm up time:	10 min 10 min
Weighing range [Max]:	30 kg 60 kg
Weighing system:	Strain gauge
Weighing units:	g kg lb oz

Display

Display digit height:	2,400 cm
-----------------------	----------

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	2 g
Minimum piece weight at piece counting (Normal):	20 g

Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	100V-240V 0.4A
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional - intern

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	870 x 480 x 150 mm
Gross weight:	12,500 kg
Net weight:	9 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	3 m
Dimensions of display device (WxDxH):	268 x 115 x 80 mm
Dimensions of weighing plate (WxDxH):	500 x 400 x 120 mm
of stand:	33 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	500 x 400 mm