

KERN FFN1K-4N



Allround-Tischwaage, geschützt durch Edelstahl und Schutzklasse IP65, auch mit Eichzulassung [M]



Power supply

Operating time (Backlight off):	50 h
Operating time (Backlight on):	30 h

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127

Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	310 x 400 x 200 mm
Gross weight:	4,080 kg
Net weight:	3,820 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Dimensions housing (WxDxH):	230 x 300 x 130 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	230 x 300 x 130 mm
Revolving screw feet:	yes
Weighing surface (WxD):	230 x 190 mm

Measuring system

Adjustment options:	External calibration
Linearity:	400 mg
Readout [d]:	200 mg
Recommended adjusting weight:	1,500 kg (M1)
Reproducibility:	200 mg
Resolution:	7500
Stabilisation time:	2 s
Tare range:	-1500000 mg
Warm up time:	30 min
Weighing range [Max]:	1,500 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,500 cm
-----------------------	----------

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	25 %

Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------