

KERN FOB0.5K-4NS

Besonders handliche Edelstahlwaage mit Schutzgrad IP65 gegen Staub und Spritzwasser



Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	255 x 195 x 75 mm
Gross weight:	886 g
Net weight:	760 g
Shipping method:	Parcel service

Construction

Casing material:	stainless steel
Dimensions housing (WxDxH):	170 x 150 x 40 mm
Dimensions of weighing plate (WxDxH):	120 x 150 x 10 mm
Material weighing plate:	stainless steel
Weighing surface (WxD):	120 x 150 mm

Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
Readout [d]:	100 mg
Recommended adjusting weight:	500 g (M1)
Reproducibility:	100 mg
Resolution:	5000
Stabilisation time:	2 s
Tare range:	500 g
Warm up time:	10 min
Weighing range [Max]:	500 g
Weighing system:	Strain gauge
Weighing units:	dwt g lb oz ozt

Display

Display digit height:	2 cm
-----------------------	------

Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	10 °C
Minimum humidity:	25 %

Power supply

Input voltage:	230 V AC 50 Hz
----------------	----------------

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	24 h
-----------------	------

Service

Adjustment at the location of installation:	961-247
---	---------

DAkKS Certificate:	963-127
--------------------	---------