



Discover more details and matching accessories online!

Compact stainless steel balance for weighing, checking and portioning in the smallest of spaces

Features

- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- High mobility: thanks to battery operation, compact, lightweight construction, it is suitable for the use in several locations (kitchen, sales office, cafeteria, food industry-laboratory etc.)
- Secure and non-slip positioning with rubber feet
- KERN FOB-NS: Protection against dust and water splashes IP65 (only when using battery)
- Your support in a HACCP-compliant quality system
- Particularly flat design
- Protective working cover included with delivery

Main scope of applications

- Food industry
- Gastronomy
- Packaging industry
- Hygiene sectors

STANDARD



1 DAY

FOB-NS

OPTION



DAkkS

Model KERN	FOB 500-1S	FOB 5K 1S	FOB 0.5K-4NS	FOB 5K-3NS
Weighing capacity [Max] g	500	5000	500	5000
Readability [d] g	0,1	1	0,1	1
Display without backlight, digit height	LCD, 20 mm		LCD, 20 mm	
Dimensions of weighing surface W×D	125×155 mm		120×150 mm	
Overall dimensions W×D×H	155×175×40 mm		150×170×40 mm	
Batteries included with delivery	9 V block		9 V block	
Operating time up to	20 h		20 h	
Net weight	0,70 kg		0,80 kg	
Permissible ambient temperature	10 °C – 40 °C		10 °C – 35 °C	10 °C – 40 °C
Option Calibr. Certificate DAkkS accr.	963-127		963-127	