

KERN HFC10T-3



Kompakte Kranwaage für den Einsatz unter rauen Umgebungsbedingungen oder beschränkten Platzverhältnissen, mit komfortablem Handterminal



Measuring system

Adjustment options:	External calibration
Linearity:	10 kg
Precision (of [Max]):	0,002
Readout [d]:	5 kg
Recommended adjusting weight:	10000 kg (M3)
Reproducibility:	5 kg
Resolution:	2000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	10 t
Weighing system:	Strain gauge
Weighing units:	kg lb N

Display

Display digit height:	2,300 cm
-----------------------	----------

Functions

Data hold function:	yes
Peak function:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Service

Adjustment at the location of installation: 961-252

DAkKS Certificate: 963-133H

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	505 x 405 x 120 mm
Gross weight:	7,400 kg
Net weight:	6 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Dimensions housing (WxDxH):	90 x 71,6 x 275 mm
Dimensions of display device (WxDxH):	88 x 64 x 256 mm