

KERN HFC 600K-1



Kompakte Kranwaage für den Einsatz unter rauen Umgebungsbedingungen oder beschränkten Platzverhältnissen, mit komfortablem Handterminal



Measuring system

Adjustment options:	External calibration
Linearity:	400 g
Precision (of [Max]):	0,002
Readout [d]:	200 g
Recommended adjusting weight:	500 kg (M3)
Reproducibility:	200 g
Resolution:	3000
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	600 kg
Weighing system:	Strain gauge
Weighing units:	kg lb N

Display

Display digit height:	2,300 cm
-----------------------	----------

Functions

Data hold function:	yes
---------------------	-----

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	40 h
Operating time (Backlight off):	30 h
Operating time (Backlight on):	15 h

Service

Adjustment at the location of installation: 961-250

DAkKS Certificate: 963-130H

Category

Brand:	KERN
Category:	Balances
Product Group:	Crane scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	505 x 395 x 120 mm
Gross weight:	2,700 kg
Net weight:	1,700 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Casing material:	aluminium
Dimensions housing (WxDxH):	90 x 55 x 255 mm