

# KERN IFS60K-2LM

Industriezählwaage mit komfortabler Zehnertastatur zur bequemen Dateneingabe, Zählauflösung 75000 Punkte



## Functions

Counting function:	yes
Function to save totals:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C

## Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	40 h
Operating time (Backlight on):	30 h
Rechargeable battery:	Rchrg. battery optional (factory)

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate:	963-129
Verification:	965-229

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	935 x 555 x 225 mm
Gross weight:	14,650 kg
Net weight:	12,450 kg
Shipping method:	Parcel service

## Construction

Cable length:	2,500 m
Cable length of display device:	3 m
Dimensions of display device (WxDxH):	260 x 150 x 65 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	10 g   20 g
Readout [d]:	10 g   20 g
Recommended adjusting weight:	60 kg (M1)
Reproducibility:	10 g   20 g
Resolution:	3 3.000
Stabilisation time:	3 s
Tare range:	60 kg
Warm up time:	10 min   10 min
Weighing range [Max]:	30 kg   60 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	1,650 cm
Display digit height:	1,300 cm

## Technical data about verification

Minimum load [Min]:	200 g   400 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	10 g   20 g

## Counting

Counting resolution:	60000
Minimum piece weight at piece counting (Laboratory):	1 g
Minimum piece weight at piece counting (Normal):	10 g
Reference weight:	yes

# KERN IFS60K-2LM



Industriezählwaage mit komfortabler Zehnertastatur zur bequemen Dateneingabe, Zählauflösung  
75000 Punkte

Dimensions of weighing plate (WxDxH):	500 x 250 x 400 mm
of stand:	33 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	500 x 250 x 400 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	500 x 400 mm