



Discover more details and matching accessories online!

1 KERN KBP-V20 IP65

Platform

Features

- Stainless steel-weighing plate, **A** Painted steel base
- 1 load cell, aluminium, silicone-coated, IP65, OIML-R60-approved, class III, 3000 e
- Level indicator and levelling feet for precise levelling of the scale, fitted as standard
- Preparation for easy assembly of the ESD earthing kit on the weighing bridge

2 KERN KFP-V20 IP65

Platform

Features

- Stainless steel-weighing plate, **B** Painted steel base
- 1 load cell, aluminium, silicone-coated, IP65, OIML-R60-approved, class III, 3000 e
- Level indicator and levelling feet for precise levelling of the scale, fitted as standard



STANDARD



FACTORY



KFB
600V20M



STANDARD



FACTORY



KFP
600V20AM

Model	Weighing capacity	Readability	Verification value	Minimal load	Cable length	Net weight	Weighing plate
	[Max] kg	[d] g	[e] g	[Min] g	approx. m	approx. kg	W×D×H mm
KERN							
1 Platform KBP-V20 IP65							
KBP 6V20LM	3 6	0,2	1 2	20 40	2,5	3,8	300×300×110
KBP 15V20M	6 15	0,5	2 5	40 100	2,5	3,8	300×240×110
KBP 15V20LM	6 15	0,5	2 5	40 100	2,5	7	400×300×110
KBP 30V20M	15 30	1	5 10	100 200	2,5	7	400×300×110
KBP 60V20M	30 60	2	10 20	200 400	2,5	8	400×300×110
KBP 60V20LM	30 60	2	10 20	200 400	2,5	13	500×400×120
KBP 150V20M	60 150	5	20 50	400 1000	2,5	13	500×400×120
KBP 150V20LM	60 150	5	20 50	400 1000	2,5	19	650×500×150
KBP 300V20M	150 300	10	50 100	1000 2000	2,5	19	650×500×150
KBP 600V20M	300 600	20	100 200	2000 4000	2,5	42	800×600×151
2 Platform KFP-V20 IP65							
KFP 3V20M	3	0,1	1	20	2,5	3,4	230×230×106
KFP 6V20M	6	0,2	1 2	20 40	2,5	4,4	230×230×106
KFP 6V20LM	6	0,2	1 2	20 40	2,5	3,8	300×240×109
KFP 15V20M	6 15	0,5	2 5	40 100	2,5	3,8	300×240×109
KFP 15V20LM	6 15	0,5	2 5	40 100	2,5	7	400×300×117
KFP 30V20SM	15 30	1	5 10	100 200	2,5	3,8	300×240×109
KFP 30V20M	15 30	1	5 10	20	2,5	7	400×300×117
KFP 30V20LM	15 30	1	5 10	20	2,5	11	500×400×127
KFP 60V20M	30 60	2	10 20	200 400	2,5	7	400×300×117
KFP 60V20LM	30 60	2	10 20	200 400	2,5	10	500×400×127
KFP 150V20M	60 150	5	20 50	400 1000	2,5	7	500×400×127
KFP 150V20LM	60 150	5	20 50	400 1000	2,5	19	650×500×139
KFP 300V20M	150 300	10	50 100	1000 2000	2,5	19	650×500×139
KFP 600V20AM	600	20	200	4000	2,5	42	800×600×192