

# KERN KFP6000V20M

Wägebrücke aus rutschfestem Stahl-Riffelblech, lackiert mit IP67



Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	1500 x 1500 mm

## Measuring system

Readout [d]:	2 kg
Resolution (non verifiable):	3000
Weighing range [Max]:	6 t

## Technical data about verification

Minimum load [Min]:	40 kg
Verification by KERN possible:	yes
Verification value [e]:	2 kg

## Service

Adjustment at the location of installation: 961-252

DAkkS Certificate:	963-132
Verification:	965-232

## Category

Brand:	KERN
Category:	Platforms
Product Group:	Weighing bridge

## Packaging & shipping

Delivery:	48 h
Dimensions packaging (WxDxH):	1550 x 1300 x 350 mm
Gross weight:	220 kg
Net weight:	208 kg
Shipping method:	Freight forwarder

## Construction

Cable length:	5 m
Dimensions of weighing plate (WxDxH):	1500 x 1500 x 130 mm