

KERN KFP60V30LM

Edelstahl-Plattform



Measuring system

Readout [d]:	2 g
Resolution (non verifiable):	30000
Weighing range [Max]:	60 kg

Technical data about verification

Minimum load [Min]:	400 g
Verification by KERN possible:	yes
Verification value [e]:	20 g

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Verification: 965-229

Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	930 x 545 x 230 mm
Gross weight:	15 kg
Net weight:	10 kg
Shipping method:	Parcel service

Construction

Cable length:	2,500 m
Dimensions of weighing plate (WxDxH):	500 x 400 x 137 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	500 x 400 mm