

# KERN KFP60V30XLM

Edelstahl-Plattform

**KERN**<sup>®</sup>



## Measuring system

Readout [d]:	2 g
Resolution (non verifiable):	30000
Weighing range [Max]:	60 kg

## Technical data about verification

Minimum load [Min]:	400 g
Verification by KERN possible:	yes
Verification value [e]:	20 g

## Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Verification: 965-229

## Category

Brand:	KERN
Category:	Platforms
Product Group:	Platform

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	1050 x 675 x 250 mm
Gross weight:	25 kg
Net weight:	22 kg
Shipping method:	Parcel service

## Construction

Cable length:	2,500 m
Dimensions of weighing plate (WxDxH):	650 x 500 x 142 mm
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	650 x 500 mm