

KERN KFT-TM

KERN Easy-Touch-Auswertegerät â die intuitive Art zu Wiegen



Measuring system

Adjustment options:	External calibration
Linearisation (points):	2
Number of weighing ranges:	2
Resolution (non verifiable):	30000
Weighing units:	g kg

Display

Display digit height:	1,200 cm
Display digit height:	1,200 cm

Functions

Capacity display:	yes
Counting function:	yes
Data hold function:	yes
Function to save totals:	yes
Help function on the display:	yes
Peak function:	yes
Percentage determination:	yes
PRE-TARE function:	yes
Standby function:	yes
Time display:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time (Backlight on):	7 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: auf Anfrage | on request

Category

Brand:	KERN
Category:	Display devices

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	300 x 200 x 150 mm
Gross weight:	1,500 g
Net weight:	1 kg
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	250 x 160 x 65 mm
Dimensions of display device (WxDxH):	250 x 160 x 65 mm
Wall mount:	yes